







**Wipdrukcontact 3-voudig 10 A 250 V~met wippen
Maakcontact 1-polig**



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 crème wit glanzend	2844 01	10	35,86	29	4010337082033
 zuiver wit glanzend	2844 03	10	35,86	29	4010337082040
 antraciet	2844 28	10	38,46	29	4010337082064
 kleur aluminium	2844 26	10	42,29	29	4010337082057
 zwart mat	2844 005	10	42,29	29	4010337037903
 grijs mat	2844 015	10	42,29	29	4010337087182
 edelstaal (gelakt)	2844 600	10	45,92	29	4010337021957

Kenmerken

- Met schroefklemmen.

Technische gegevens

Inbouwdiepte: 25 mm

Aansluitingdoorsnede
- voor geleiders tot: 2.5mm²

Aanwijzingen

- Uitsluitend voor schroefbevestiging.
