


Wipschakelaar 10 AX 250 V~ met wip 2-voudig voor weergave hotelkamerstatus



| Specificatie | Art. nr. | VE | EUR/stuk excl. BTW | PS | EAN |
|---|----------|----|--------------------|----|---------------|
|  crème wit glanzend | 3104 01 | 1 | 48,09 | 01 | 4010337042495 |
|  zuiver wit glanzend | 3104 03 | 1 | 48,09 | 01 | 4010337042501 |
|  zuiver wit mat | 3104 27 | 1 | 48,09 | 01 | 4010337042525 |
|  antraciet | 3104 28 | 1 | 48,69 | 11 | 4010337042532 |
|  kleur aluminium | 3104 26 | 1 | 52,66 | 11 | 4010337042518 |
|  zwart mat | 3104 005 | 1 | 52,66 | 11 | 4010337069812 |

Kenmerken

- Schakelaar voor weergave hotelkamerstatus "Do not disturb" en "Make up room".
- Met vergrendeling tegen dubbelzijdig inschakelen.
- Elektrisch en mechanisch vergrendeld.

Technische gegevens

| | |
|---|---------------------|
| Inbouwdiepte: | 32 mm |
| Aansluitingdoorsnede - voor massieve en soepele geleiders tot: | 2,5 mm ² |

Nominaal vermogen
- LEDi/ CFLi:

100 W
