











## Wip voor wippenet 2-voudig voor tastsensor 4.95



| Specificatie   | Art. nr. | VE | EUR/stuk excl. BTW | PS | EAN           |
|--|----------|----|--------------------|----|---------------|
|  aluminium zuiver wit glanzend (gelakt) | 8332 903 | 1  | 55,07              | 06 | 4010337098713 |
|  aluminium zuiver wit mat (gelakt)    | 8332 927 | 1  | 55,07              | 06 | 4010337098737 |
|  aluminium antraciet (gelakt)         | 8332 928 | 1  | 55,07              | 06 | 4010337098676 |
|  aluminium (geanodiseerd)             | 8332 17  | 1  | 43,48              | 06 | 4010337096979 |
|  aluminium zwart mat (gelakt)         | 8332 905 | 1  | 55,07              | 06 | 4010337098690 |
|  aluminium grijs mat (gelakt)         | 8332 915 | 1  | 55,07              | 06 | 4010337098652 |
|  aluminium zwart (geanodiseerd)       | 8332 126 | 1  | 43,48              | 06 | 4010337096993 |
|  brons                                | 8332 38  | 1  | 92,75              | 06 | 4010337098751 |
|  glas wit                             | 8332 12  | 1  | 43,48              | 06 | 4010337097792 |

|   |            |          |   |       |    |               |
|---|------------|----------|---|-------|----|---------------|
|  | glas zwart | 8332 05  | 1 | 43,48 | 06 | 4010337098027 |
|  | edelstaal  | 8332 219 | 1 | 75,36 | 06 | 4010337097334 |