












## Wip voor wippenet 4-voudig voor tastsensor 4.95



Specificatie	Art. nr.	VE	EUR/stuk excl. BTW	PS	EAN
 aluminium zuiver wit glanzend (gelakt)	8334 903	1	43,48	06	4010337098720
 aluminium zuiver wit mat (gelakt)	8334 927	1	43,48	06	4010337098744
 aluminium antraciet (gelakt)	8334 928	1	43,48	06	4010337098683
 aluminium (geanodiseerd)	8334 17	1	31,89	06	4010337096986
 aluminium zwart mat (gelakt)	8334 905	1	43,48	06	4010337098706
 aluminium grijs mat (gelakt)	8334 915	1	43,48	06	4010337098669
 aluminium zwart (geanodiseerd)	8334 126	1	31,89	06	4010337097228
 brons	8334 38	1	75,36	06	4010337098775
 glas wit	8334 12	1	31,89	06	4010337098010

---

 glas zwart	8334 05	1	31,89	06	4010337098034
<hr/>					
 edelstaal	8334 219	1	57,97	06	4010337097785
<hr/>					