






## Trykkbryter 10 AX 250 V~med rett vippe Universal-utkoblingsvendebryter



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 renhvit glans	0121 201 1404605	1/5	01	4010337052692
 antrasitt	0121 28	1/5	11	4010337029335
 aluminiumsfarget	0121 26	1	11	4010337029328
 svart matt	0121 005	1	11	4010337037972
 grå matt	0121 015	1	11	4010337077091
 rustfritt stål	0121 600 1479211	1/5	11	4010337021261

### Tekniske data

Monteringsdybde: 28 mm

Tilkoblingstverrsnitt  
- for stive og fleksible ledere opptil: 2,5 mm<sup>2</sup>

Nominell effekt  
- LEDi/CFLi: 100 W

## **Merknader**

- Avhengig av tilgjengelighet.

---