







## Trykk-kontrollbryter 10 AX 250 V~ med vippe Utkoblingsbryter 2-polet



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 kremhvit glans	0122 01 1420012	1/5	01	4010337122012
 renhvit glans	0122 03 1420062	1/5	01	4010337122036
 antrasitt	0122 28 1420051	1/5	11	4010337122289
 aluminiumsfarget	0122 26 1420049	1/5	11	4010337122265
 svart matt	0122 005 1405002	1/5	11	4010337037934
 rustfritt stål	0122 600	1/5	11	4010337021773

### Tekniske data

Monteringsdybde:	28 mm
Tilkoblingstverrsnitt - for stive og fleksible ledere opptil:	2,5 mm <sup>2</sup>
Nominell effekt - LEDi/CFLi:	100 W

## **Merknader**

- Kan også kobles til med belysningsmulighet.
  - Avhengig av tilgjengelighet.
- 

## **Leveringsomfang**

- Glimlampeelement 230 V~, 1,5 mA inkludert.
-