

Trykkbryter 10 AX 250 V~med rett vippe Mellomvender



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 renhvit glans	0123 201 1404608	1/5	01	4010337052708
 antrasitt	0123 28	1/5	11	4010337029366
 aluminiumsfarget	0123 26	1	11	4010337029359
 svart matt	0123 005	1	11	4010337037996
 grå matt	0123 015	1	11	4010337077114
 rustfritt stål	0123 600	1	11	4010337021254

Tekniske data

Monteringsdybde:	28 mm
Tilkoblingstverrsnitt - for stive og fleksible ledere opptil:	2,5 mm ²
Nominell effekt - LEDi/CFLi:	100 W

Merknader

- Avhengig av tilgjengelighet.
