








Trykkbryter 10 AX 250 V~ med dobbel vippe Kronevender



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 kremhvitt glans	0125 01 1420022	1/5	01	4010337125013
 renhvitt glans	0125 03 1420063	1/5	01	4010337125037
 antrasitt	0125 28 1420058	1/5	11	4010337125280
 aluminiumsfarget	0125 26 1420056	1/5	11	4010337125266
 svart matt	0125 005	1/5	11	4010337038016
 grå matt	0125 015	1/5	11	4010337077138
 rustfritt stål	0125 600	1/5	11	4010337021780

Tekniske data

Monteringsdybde

- 0125 ... 28 mm
- 0128 ... 32 mm

Tilkoblingstverrsnitt

- for stive og fleksible ledere opptil: 2,5 mm²

Nominell effekt

- LEDi/CFLi: 100 W

Illustrasjonene kan avvike fra originalen.

Merknader

- Avhengig av tilgjengelighet.
