









Trykkbryter 10 AX 250 V~ med vippe Universal-utkoblingsvendebryter



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 kremhvitt glans	0126 01 1420032	1/5	01	4010337126010
 renhvitt glans	0126 03 1420064	1/5	01	4010337126034
 antrasitt	0126 28 1420238	1/5	11	4010337126287
 aluminiumsfarget	0126 26 1420236	1/5	11	4010337126263
 svart matt	0126 005	1/5	11	4010337037965
 grå matt	0126 015	1/5	11	4010337077145
 rustfritt stål	0126 600	1/5	11	4010337021742

Tekniske data

Monteringsdybde:	28 mm
Tilkoblingstverrsnitt - for stive og fleksible ledere opptil:	2,5 mm ²
Nominell effekt - LEDi/CFLi:	100 W

Merknader

- Avhengig av tilgjengelighet.
