








Trykkbryter 10 AX 250 V~ med vippe Universal-utkoblingsvendebryter



| Spesifikasjon | Bestillings nr. | PE | PS | EAN |
|--|--------------------|-----|----|---------------|
|  kremhvit glans | 0126 01 1420032 | 1/5 | 01 | 4010337126010 |
|  renhvit glans | 0126 03 1420064 | 1/5 | 01 | 4010337126034 |
|  antrasitt | 0126 28 1420238 | 1/5 | 11 | 4010337126287 |
|  aluminiumsfarget | 0126 26 1420236 | 1/5 | 11 | 4010337126263 |
|  svart matt | 0126 005 | 1/5 | 11 | 4010337037965 |
|  grå matt | 0126 015 | 1/5 | 11 | 4010337077145 |
|  rustfritt stål | 0126 600 | 1/5 | 11 | 4010337021742 |

Tekniske data

| | |
|--|---------------------|
| Monteringsdybde: | 28 mm |
| Tilkoblingstverrsnitt - for stive og fleksible ledere opptil: | 2,5 mm ² |
| Nominell effekt - LEDi/CFLi: | 100 W |

Merknader

- Avhengig av tilgjengelighet.
