

Trykkbryter 10 AX 250 V~ med vippe Mellomvender



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 kremhvit glans	0127 01 1420042	1/5	01	4010337127017
 renhvit glans	0127 03 1420065	1/5	01	4010337127031
 antrasitt	0127 28 1420245	1/5	11	4010337127284
 aluminiumsfarget	0127 26 1420243	1/5	11	4010337127260
 svart matt	0127 005	1/5	11	4010337037989
 grå matt	0127 015	1/5	11	4010337077169
 rustfritt stål	0127 600	1/5	11	4010337021759
 bronse	0127 603	1/5	11	4010337106067

Tekniske data

Monteringsdybde: 28 mm

Tilkoblingstverrsnitt
- for stive og fleksible ledere opptil: 2,5 mm²

Illustrasjonene kan avvike fra originalen.

Nominell effekt
- LEDi/CFLi:

100 W
