








**Trykkbryter 10 AX 250 V~ med dobbel vippe
Vendebryter, dobbel**

Spesifikasjon	Bestillings nr.	PE	PS	EAN
 kremhvitt glans	0128 01 1420059	1/5	01	4010337128014
 renhvitt glans	0128 03 1420066	1/5	01	4010337128038
 antrasitt	0128 28 1420252	1/5	11	4010337128281
 aluminiumsfarget	0128 26 1420250	1/5	11	4010337128267
 svart matt	0128 005	1/5	11	4010337038030
 grå matt	0128 015	1/5	11	4010337077176
 rustfritt stål	0128 600	1/5	11	4010337021797

Tekniske data

Monteringsdybde

- 0125 ... 28 mm
- 0128 ... 32 mm

Tilkoblingstverrsnitt

- for stive og fleksible ledere opptil: 2,5 mm²

Nominell effekt

- LEDi/CFLi: 100 W

Illustrasjonene kan avvike fra originalen.

Merknader

- Avhengig av tilgjengelighet.
