








**Trykk-kontrollbryter 10 AX 250 V~ med vippe
Universal-utkoblingsvendebryter**



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 kremhvit glans	0136 01 1420060	1/5	01	4010337136019
 renhvit glans	0136 03 1420067	1/5	01	4010337136033
 antrasitt	0136 28 1420260	1/5	11	4010337136286
 aluminiumsfarget	0136 26 1420258	1/5	11	4010337136262
 svart matt	0136 005	1/5	11	4010337037941
 grå matt	0136 015	1/5	11	4010337077190
 rustfritt stål	0136 600	1/5	11	4010337021766

Tekniske data

Monteringsdybde:	28 mm
Tilkoblingstverrsnitt - for stive og fleksible ledere opptil:	2,5 mm ²
Nominell effekt - LEDi/CFLi:	100 W

Illustrasjonene kan avvike fra originalen.

Merknader

- Kan også kobles til med belysningsmulighet.
- Avhengig av tilgjengelighet.

Leveringsomfang

- Glimlampeelement 230 V~, 1,5 mA inkludert.
-