








Trykk-kontrollbryter 10 AX 250 V~ med vippe Universal-utkoblingsvendebryter



| Spesifikasjon | Bestillings nr. | PE | PS | EAN |
|--|--------------------|-----|----|---------------|
|  kremhvit glans | 0136 01 1420060 | 1/5 | 01 | 4010337136019 |
|  renhvit glans | 0136 03 1420067 | 1/5 | 01 | 4010337136033 |
|  antrasitt | 0136 28 1420260 | 1/5 | 11 | 4010337136286 |
|  aluminiumsfarget | 0136 26 1420258 | 1/5 | 11 | 4010337136262 |
|  svart matt | 0136 005 | 1/5 | 11 | 4010337037941 |
|  grå matt | 0136 015 | 1/5 | 11 | 4010337077190 |
|  rustfritt stål | 0136 600 | 1/5 | 11 | 4010337021766 |

Tekniske data

| | |
|--|---------------------|
| Monteringsdybde: | 28 mm |
| Tilkoblingstverrsnitt - for stive og fleksible ledere opptil: | 2,5 mm ² |
| Nominell effekt - LEDi/CFLi: | 100 W |

Merknader

- Kan også kobles til med belysningsmulighet.
- Avhengig av tilgjengelighet.

Leveringsomfang

- Glimlampeelement 230 V~, 1,5 mA inkludert.
-