








## Dekkramme Gira E2 svart matt



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	0211 09 1499901	10	11	4010337036739
 1,5-dobbel	1001 09	10	11	4010337072775
 Dobbel	0212 09 1499902	10	11	4010337036760
 dobbel, uten mellomstykke	1002 09 1499903	10	11	4010337036784
 3-dobbel	0213 09 1499904	1/5	11	4010337036821
 4-dobbel	0214 09 1499905	1/5	11	4010337036869
 5-dobbel	0215 09 1499906	1	11	4010337036906

### Merknader

- Også egnet for kanalinstallasjoner.
- Dekkramme (enkel til 5-dobbel) i kombinasjon med tetningssett også egnet for vannbeskyttet innfelt montering IP44.