








Dekkramme Gira E2 renhvit silkematt



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	0211 22 1420510	10/100	01	4010337211228
 1,5-dobbel	1001 22 1522590	10	01	4010337881322
 Dobbel	0212 22 1420512	10/100	01	4010337212225
 dobbel, uten mellomstykke	1002 22 1420204	10	01	4010337002222
 3-dobbel	0213 22 1420514	1/5	01	4010337213222
 4-dobbel	0214 22 1420516	1/5	01	4010337214229
 5-dobbel	0215 22 1420518	1/5	01	4010337215226

Merknader

- Også egnet for kanalinstallasjoner.
- Dekkramme (enkel til 5-dobbel) i kombinasjon med tetningssett også egnet for vannbeskyttet innfelt montering IP44.