







## Dekkramme Gira E2 rustfritt stål



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	0211 33 1479215	10	11	4010337019794
 Dobbel	0212 33 1479206	10	11	4010337019800
 dobbel, uten mellomstykke	1002 33 1479230	10	11	4010337019848
 3-dobbel	0213 33 1479218	1/5	11	4010337019817
 4-dobbel	0214 33 1479219	1/5	11	4010337019824
 5-dobbel	0215 33 1479228	1/5	11	4010337019831

### Merknader

- Også egnet for kanalinstallasjoner.
- Dekkramme (enkel til 5-dobbel) i kombinasjon med tetningssett også egnet for vannbeskyttet innfelt montering IP44.