







Dekkramme Gira E2 rustfritt stål



| Spesifikasjon | Bestillings nr. | PE | PS | EAN |
|---|--------------------|-----|----|---------------|
|  Enkel | 0211 33 1479215 | 10 | 11 | 4010337019794 |
|  Dobbel | 0212 33 1479206 | 10 | 11 | 4010337019800 |
|  dobbel, uten mellomstykke | 1002 33 1479230 | 10 | 11 | 4010337019848 |
|  3-dobbel | 0213 33 1479218 | 1/5 | 11 | 4010337019817 |
|  4-dobbel | 0214 33 1479219 | 1/5 | 11 | 4010337019824 |
|  5-dobbel | 0215 33 1479228 | 1/5 | 11 | 4010337019831 |

Merknader

- Også egnet for kanalinstallasjoner.
- Dekkramme (enkel til 5-dobbel) i kombinasjon med tetningssett også egnet for vannbeskyttet innfelt montering IP44.