









## Dekkramme Gira E2 grå matt



| Spesifikasjon   | Bestillings nr. | PE  | PS | EAN           |
|---|-----------------|-----|----|---------------|
|  Enkel                      | 0211 37         | 10  | 11 | 4010337077299 |
|  1,5-dobbel                | 1001 37         | 10  | 11 | 4010337082422 |
|  Dobbel                    | 0212 37         | 10  | 11 | 4010337077589 |
|  dobbel, uten mellomstykke | 1002 37         | 10  | 11 | 4010337082439 |
|  3-dobbel                  | 0213 37         | 1/5 | 11 | 4010337077602 |
|  4-dobbel                  | 0214 37         | 1/5 | 11 | 4010337077626 |
|  5-dobbel                  | 0215 37         | 1   | 11 | 4010337077640 |

### Merknader

- Også egnet for kanalinstallasjoner.
- Dekkramme (enkel til 5-dobbel) i kombinasjon med tetningssett også egnet for vannbeskyttet innfelt montering IP44.