








Dekkramme Gira E3 renhvit glans med bæreramme renhvit glans



| Spesifikasjon | Bestillings nr. | PE | PS | EAN |
|---|---------------------|-----|----|---------------|
|  Enkel | 0211 410 1403512 | 10 | 11 | 4010337023715 |
|  Dobbel | 0212 410 1403529 | 10 | 11 | 4010337023722 |
|  dobbel, uten mellomstykke | 1002 410 1403546 | 10 | 11 | 4010337023760 |
|  3-dobbel | 0213 410 1403563 | 1/5 | 11 | 4010337023739 |
|  4-dobbel | 0214 410 1403580 | 1/5 | 11 | 4010337023746 |
|  5-dobbel | 0215 410 1403597 | 1 | 11 | 4010337023753 |

Egenskaper

- Bruddsikker.