







**Dekkramme Gira E3**  
mørkgrå soft-touch med bæreramme renhvit glans



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	0211 413 1403517	10	11	4010337024026
 Dobbel	0212 413 1403534	10	11	4010337024033
 dobbel, uten mellomstykke	1002 413 1403551	10	11	4010337024071
 3-dobbel	0213 413 1403568	1/5	11	4010337024040
 4-dobbel	0214 413 1403585	1/5	11	4010337024057
 5-dobbel	0215 413 1479284	1	11	4010337024064

### Egenskaper

- Bruddsikker.

### Merknader

- Soft-touch-overflate.  
- NCS-verdi: lign. NCS S 7000-N