








## Dekkramme Gira E2 aluminiumsfarget



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	0211 25 1420521	10/100	11	4010337211259
 1,5-dobbel	1001 25 1522592	10	11	4010337881346
 Dobbel	0212 25 1420562	10	11	4010337212256
 dobbel, uten mellomstykke	1002 25 1420207	10	11	4010337002253
 3-dobbel	0213 25 1420599	1/5	11	4010337213253
 4-dobbel	0214 25 1420630	1/5	11	4010337214250
 5-dobbel	0215 25 1420662	1/5	11	4010337215257

### Merknader

- Også egnet for kanalinstallasjoner.
- Dekkramme (enkel til 5-dobbel) i kombinasjon med tetningssett også egnet for vannbeskyttet innfelt montering IP44.