







Dekkramme Gira E3 lysegrå soft-touch med bæreramme renhvit glans



| Spesifikasjon | Bestillings nr. | PE | PS | EAN |
|---|---------------------|-----|----|---------------|
|  Enkel | 0211 411 1403513 | 10 | 11 | 4010337023777 |
|  Dobbel | 0212 411 1403530 | 10 | 11 | 4010337023784 |
|  dobbel, uten mellomstykke | 1002 411 1403547 | 10 | 11 | 4010337023821 |
|  3-dobbel | 0213 411 1403564 | 1/5 | 11 | 4010337023791 |
|  4-dobbel | 0214 411 1403581 | 1 | 11 | 4010337023807 |
|  5-dobbel | 0215 411 1403598 | 1/5 | 11 | 4010337023814 |

Egenskaper

- Bruddsikker.

Merknader

- Soft-touch-overflate.
- NCS-verdi: lign. NCS S-2000 N