








Dekkramme Gira Standard 55 kremhvit glans



| Spesifikasjon | Bestillings nr. | PE | PS | EAN |
|---|--------------------|--------|----|---------------|
|  Enkel | 0211 01 1420705 | 10/100 | 21 | 4010337211013 |
|  1,5-dobbel | 1001 01 | 10 | 01 | 4010337881247 |
|  Dobbel | 0212 01 1420706 | 10/100 | 21 | 4010337212010 |
|  dobbel, uten mellomstykke | 1002 01 | 10 | 01 | 4010337002017 |
|  3-dobbel | 0213 01 1420707 | 10/100 | 01 | 4010337213017 |
|  4-dobbel | 0214 01 1420708 | 1/5 | 01 | 4010337214014 |
|  5-dobbel | 0215 01 1420709 | 1/5 | 01 | 4010337215011 |

Egenskaper

- Bruddsikker.

Merknader

- Også egnet for kanalinstallasjoner.
 - Dekkramme (enkel til 5-dobbel) i kombinasjon med tetningssett også egnet for vannbeskyttet innfelt montering IP44.
-