







## Dekkramme Gira E3 renhvit glans med bæreramme renhvit glans



| Spesifikasjon   | Bestillings nr.     | PE  | PS | EAN           |
|---|---------------------|-----|----|---------------|
|  Enkel                      | 0211 410<br>1403512 | 10  | 11 | 4010337023715 |
|  Dobbel                    | 0212 410<br>1403529 | 10  | 11 | 4010337023722 |
|  dobbel, uten mellomstykke | 1002 410<br>1403546 | 10  | 11 | 4010337023760 |
|  3-dobbel                  | 0213 410<br>1403563 | 1/5 | 11 | 4010337023739 |
|  4-dobbel                  | 0214 410<br>1403580 | 1/5 | 11 | 4010337023746 |
|  5-dobbel                  | 0215 410<br>1403597 | 1   | 11 | 4010337023753 |

### Egenskaper

- Bruddsikker.