





## Dekkramme Gira E3 grå soft-touch med bæreramme antrasitt



| Spesifikasjon   | Bestillings nr.     | PE  | PS | EAN           |
|---|---------------------|-----|----|---------------|
|  Enkel                      | 0211 422<br>1403516 | 10  | 11 | 4010337023951 |
|  Dobbel                    | 0212 422<br>1403533 | 10  | 11 | 4010337023968 |
|  dobbel, uten mellomstykke | 1002 422<br>1403550 | 10  | 11 | 4010337024019 |
|  3-dobbel                  | 0213 422<br>1403567 | 1/5 | 11 | 4010337023975 |
|  4-dobbel                  | 0214 422<br>1403584 | 1/5 | 11 | 4010337023982 |
|  5-dobbel                  | 0215 422<br>1479283 | 1/5 | 11 | 4010337023999 |

### Egenskaper

- Bruddsikker.

### Merknader

- Soft-touch-overflate.  
- NCS-verdi: lign. NCS S 3500-N