








## Adapterramme med kvadratisk utsparing for apparater med deksel (50 x 50 mm)



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 kremhvit glans	0282 01	5/25	01	4010337282013
 renhvit glans	0282 03	5/25	01	4010337282037
 antrasitt	0282 28	5/25	11	4010337282280
 aluminiumsfarget	0282 26	5/25	11	4010337282266
 svart matt	0282 005	5/25	11	4010337036951
 grå matt	0282 015	5/25	11	4010337078999
 rustfritt stål (lakkert)	0282 600	5/25	11	4010337022015

### Egenskaper

- Med adapterrammen og dekkrammen (enkel- til 5-dobbel) kan eksterne apparater med kvadratisk sentralplate (50 x 50 mm) f. eks. fra Alcatel, AMP Econo Link System, Brand-Rex, BTR, Cellpack ITT Cannon Cat. 5, Deutsche Telekom, Drahtex, Hirose, Kannegieter BICC Brand Rex, Kerpen ELine 600, Krone, Molex, Nedap, Panduit, Quante, Reichle de Massari, Rutenbeck, Schumann Netzwerktechnik, HomeWay, Siemens ICCS 100, 300 og 600, Telegärtner, Telenorma, TKM (4 x RJ45) skjermet, Cat.5), osv. integreres i bryterprogrammet.