








Adapterramme med kvadratisk utsparing for apparater med deksel (50 x 50 mm)



| Spesifikasjon | Bestillings nr. | PE | PS | EAN |
|--|-----------------|------|----|---------------|
|  kremhvitt glans | 0282 01 | 5/25 | 01 | 4010337282013 |
|  renhvitt glans | 0282 03 | 5/25 | 01 | 4010337282037 |
|  antrasitt | 0282 28 | 5/25 | 11 | 4010337282280 |
|  aluminiumsfarget | 0282 26 | 5/25 | 11 | 4010337282266 |
|  svart matt | 0282 005 | 5/25 | 11 | 4010337036951 |
|  grå matt | 0282 015 | 5/25 | 11 | 4010337078999 |
|  rustfritt stål (lakkert) | 0282 600 | 5/25 | 11 | 4010337022015 |

Egenskaper

- Med adapterrammen og dekkrammen (enkel- til 5-dobbel) kan eksterne apparater med kvadratisk sentralplate (50 x 50 mm) f. eks. fra Alcatel, AMP Econo Link System, Brand-Rex, BTR, Cellpack ITT Cannon Cat. 5, Deutsche Telekom, Drahtex, Hirose, Kannegieter BICC Brand Rex, Kerpen ELine 600, Krone, Molex, Nedap, Panduit, Quante, Reichle de Massari, Rutenbeck, Schumann Netzwerktechnik, HomeWay, Siemens ICCS 100, 300 og 600, Telegärtner, Telenorma, TKM (4 x RJ45) skjermet, Cat.5), osv. integreres i bryterprogrammet.