








Vippe



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 kremhvit glans	0296 01	10	21	4010337296010
 renhvit glans	0296 03 1420427	10/100	21	4010337296034
 antrasitt	0296 28 1420490	10/100	11	4010337296287
 aluminiumsfarget	0296 26 1420488	10	11	4010337296263
 svart matt	0296 005 1421101	10	11	4010337038061
 grå matt	0296 015	10	11	4010337080220
 rustfritt stål	0296 600 1479208	10	11	4010337021667

Merknader

- Dekkramme (enkel til 5-dobbelt) fra bryterprogrammene Standard 55 og Gira E2 i forbindelse med tetningssettet også egnet for installasjon av vippebryter og vippetrykknapp beskyttet mot vannsprut IP44 (gjelder ikke for vippe dobbel).
- Avhengig av tilgjengelighet.