






## Dekkramme Gira E2 for flat innbygging antrasitt



| Spesifikasjon  | Bestillings nr.     | PE  | PS | EAN           |
|--|---------------------|-----|----|---------------|
|  Enkel                       | 0211 235<br>1479244 | 10  | 11 | 4010337021278 |
|  Dobbelt                    | 0212 235<br>1479245 | 10  | 11 | 4010337021285 |
|  dobbelt, uten mellomstykke | 1002 235<br>1479248 | 10  | 11 | 4010337021315 |
|  3-dobbelt                  | 0213 235<br>1479246 | 1/5 | 11 | 4010337021292 |
|  4-dobbelt                  | 0214 235<br>1479247 | 1/5 | 11 | 4010337021308 |