








Dekkramme Gira E2 aluminiumsfarget



| Spesifikasjon | Bestillings nr. | PE | PS | EAN |
|---|--------------------|--------|----|---------------|
|  Enkel | 0211 25 1420521 | 10/100 | 11 | 4010337211259 |
|  1,5-dobbel | 1001 25 1522592 | 10 | 11 | 4010337881346 |
|  Dobbel | 0212 25 1420562 | 10 | 11 | 4010337212256 |
|  dobbel, uten mellomstykke | 1002 25 1420207 | 10 | 11 | 4010337002253 |
|  3-dobbel | 0213 25 1420599 | 1/5 | 11 | 4010337213253 |
|  4-dobbel | 0214 25 1420630 | 1/5 | 11 | 4010337214250 |
|  5-dobbel | 0215 25 1420662 | 1/5 | 11 | 4010337215257 |

Merknader

- Også egnet for kanalinstallasjoner.
- Dekkramme (enkel til 5-dobbel) i kombinasjon med tetningssett også egnet for vannbeskyttet innfelt montering IP44.