






**Dekkramme Gira Standard 55 med tekstfelt  
kremhvit glans**



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	1091 01	10	01	4010337091011
 Dobbel horisontal	1092 01	10	01	4010337092018
 Dobbel lodrett	1102 01	10	01	4010337102014
 3-dobbel horisontal	1093 01	1/5	01	4010337093015
 3-dobbel vertikal	1103 01	1/5	01	4010337103011
 4-dobbel horisontal	1094 01	1/5	01	4010337094012
 4-dobbel loddrett	1114 01	1	01	4010337008903
 5-dobbel horisontal	1095 01	1	01	4010337095019
 5-dobbel loddrett	1115 01	1	01	4010337115014

## Egenskaper

- Bruddsikker.
  - Sprøytetåketett.
  - Dekkramme med transparent vindu for merking av innsatsene.
  - Spesielt egnet for objekter som krever merking og dokumentasjon av elektroinstallasjon, f.eks. innen forvaltning, næringsvirksomhet, på flyplasser, i bedrifter og på sykehus.
- 

## Merknader

- Må ikke brukes sammen med: tetningssett IP44, påveggboks av flat konstruksjon, påveggboks.
-