










**Dekkramme Gira Standard 55 med tekstfelt
renhvit glans**



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	1091 03	10	01	4010337091035
 Dobbel horisontal	1092 03	10	01	4010337092032
 Dobbel lodrett	1102 03	10	01	4010337102038
 3-dobbel horisontal	1093 03	10	01	4010337093039
 3-dobbel vertikal	1103 03	1/5	01	4010337103035
 4-dobbel horisontal	1094 03	1/5	01	4010337094036
 4-dobbel loddrett	1114 03	1/5	01	4010337008910
 5-dobbel horisontal	1095 03	1/5	01	4010337095033
 5-dobbel loddrett	1115 03	1/5	01	4010337115038

Egenskaper

- Bruddsikker.
 - Sprøytetåketett.
 - Dekkramme med transparent vindu for merking av innsatsene.
 - Spesielt egnet for objekter som krever merking og dokumentasjon av elektroinstallasjon, f.eks. innen forvaltning, næringsvirksomhet, på flyplasser, i bedrifter og på sykehus.
-

Merknader

- Må ikke brukes sammen med: tetningssett IP44, påveggboks av flat konstruksjon, påveggboks.
-