










Ramme Gira E2 med tekstfelt aluminiumsfarget



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	1091 25	10	11	4010337084051
 2-hull vannrett	1092 25	10	11	4010337084112
 2-hull loddrett	1102 25	10	11	4010337084143
 3-hull horisontal	1093 25	1/5	11	4010337084181
 3-hull loddrett	1103 25	1/5	11	4010337084228
 4-hull horisontal	1094 25	1/5	11	4010337084266
 4-hull loddrett	1114 25	1/5	11	4010337084303
 5-hull vannrett	1095 25	1	11	4010337084389
 5-hull loddrett	1115 25	1/5	11	4010337084341

Egenskaper

- Bruddsikker.
 - Sprøytetåketett.
 - Ramme med transparent vindu for merking av innsatsene.
 - Spesielt egnet for objekter som krever merking og dokumentasjon av elektroinstallasjon, f.eks. innen forvaltning, næringsvirksomhet, på flyplasser, i bedrifter og på sykehus.
-

Merknader

- Må ikke brukes sammen med: tetningssett IP44, påveggboks av flat konstruksjon, påveggboks.
-