










**Ramme Gira E2 med tekstfelt
renhvit glanset**



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	1091 29	10	01	4010337084068
 2-hull vannrett	1092 29	10	01	4010337084129
 2-hull loddrett	1102 29	10	01	4010337084150
 3-hull horisontal	1093 29	1/5	01	4010337084198
 3-hull loddrett	1103 29	1/5	01	4010337084235
 4-hull horisontal	1094 29	1	01	4010337084273
 4-hull loddrett	1114 29	1	01	4010337084310
 5-hull vannrett	1095 29	1/5	01	4010337084396
 5-hull loddrett	1115 29	1/5	01	4010337084358

Egenskaper

- Bruddsikker.
 - Sprøytetåketett.
 - Ramme med transparent vindu for merking av innsatsene.
 - Spesielt egnet for objekter som krever merking og dokumentasjon av elektroinstallasjon, f.eks. innen forvaltning, næringsvirksomhet, på flyplasser, i bedrifter og på sykehus.
-

Merknader

- Må ikke brukes sammen med: tetningssett IP44, påveggboks av flat konstruksjon, påveggboks.
-