










**Dekkramme Gira E2 med tekstfelt  
renhvit glans**



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	1091 29	10	01	4010337084068
 Dobbel horisontal	1092 29	10	01	4010337084129
 Dobbel lodrett	1102 29	10	01	4010337084150
 3-dobbel horisontal	1093 29	1/5	01	4010337084198
 3-dobbel vertikal	1103 29	1/5	01	4010337084235
 4-dobbel horisontal	1094 29	1	01	4010337084273
 4-dobbel loddrett	1114 29	1	01	4010337084310
 5-dobbel horisontal	1095 29	1/5	01	4010337084396
 5-dobbel loddrett	1115 29	1/5	01	4010337084358

## Egenskaper

- Bruddsikker.
  - Sprøytetåketett.
  - Dekkramme med transparent vindu for merking av innsatsene.
  - Spesielt egnet for objekter som krever merking og dokumentasjon av elektroinstallasjon, f.eks. innen forvaltning, næringsvirksomhet, på flyplasser, i bedrifter og på sykehus.
- 

## Merknader

- Må ikke brukes sammen med: tetningssett IP44, påveggboks av flat konstruksjon, påveggboks.
-