











Dekkramme Gira E2 med tekstfelt grå matt



| Spesifikasjon | Bestillings nr. | PE | PS | EAN |
|---|-----------------|----|----|---------------|
|  Enkel | 1091 37 | 10 | 11 | 4010337082590 |
|  Dobbel vannrett | 1092 37 | 10 | 11 | 4010337082651 |
|  Dobbel lodrett | 1102 37 | 10 | 11 | 4010337082699 |
|  3-dobbel vannrett | 1093 37 | 1 | 11 | 4010337082668 |
|  3-dobbel vertikal | 1103 37 | 1 | 11 | 4010337082729 |
|  4-dobbel vannrett | 1094 37 | 1 | 11 | 4010337082675 |
|  4-dobbel loddrett | 1114 37 | 1 | 11 | 4010337082873 |
|  5-dobbel vannrett | 1095 37 | 1 | 11 | 4010337082682 |
|  5-dobbel loddrett | 1115 37 | 1 | 11 | 4010337082880 |

Egenskaper

- Bruddsikker.
 - Sprøytetåketett.
 - Dekkramme med transparent vindu for merking av innsatsene.
 - Spesielt egnet for objekter som krever merking og dokumentasjon av elektroinstallasjon, f.eks. innen forvaltning, næringsvirksomhet, på flyplasser, i bedrifter og på sykehus.
-

Merknader

- Må ikke brukes sammen med: tetningssett IP44, påveggghus av flat konstruksjon, påveggghus.
-