


Dekkramme Gira Standard 55 med tekstfelt renhvit glans



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	1091 03	10	01	4010337091035
 Dobbel horisontal	1092 03	10	01	4010337092032
 Dobbel lodrett	1102 03	10	01	4010337102038
 3-dobbel horisontal	1093 03	10	01	4010337093039
 3-dobbel vertikal	1103 03	1/5	01	4010337103035
 4-dobbel horisontal	1094 03	1/5	01	4010337094036
 4-dobbel loddrett	1114 03	1/5	01	4010337008910
 5-dobbel horisontal	1095 03	1/5	01	4010337095033
 5-dobbel loddrett	1115 03	1/5	01	4010337115038

Egenskaper

- Bruddsikker.
 - Sprøytetåketett.
 - Dekkramme med transparent vindu for merking av innsatsene.
 - Spesielt egnet for objekter som krever merking og dokumentasjon av elektroinstallasjon, f.eks. innen forvaltning, næringsvirksomhet, på flyplasser, i bedrifter og på sykehus.
-

Merknader

- Må ikke brukes sammen med: tetningssett IP44, påveggboks av flat konstruksjon, påveggboks.
-