


## Dekkramme Gira E2 med tekstfelt svart matt



| Spesifikasjon   | Bestillings nr. | PE  | PS | EAN           |
|---|-----------------|-----|----|---------------|
|  Enkel                | 1091 09         | 10  | 11 | 4010337036746 |
|  Dobbel horisontal   | 1092 09         | 10  | 11 | 4010337036814 |
|  Dobbel lodrett      | 1102 09         | 10  | 11 | 4010337036807 |
|  3-dobbel horisontal | 1093 09         | 1/5 | 11 | 4010337036852 |
|  3-dobbel vertikal   | 1103 09         | 1/5 | 11 | 4010337036845 |
|  4-dobbel horisontal | 1094 09         | 1/5 | 11 | 4010337036890 |
|  4-dobbel loddrett   | 1114 09         | 1   | 11 | 4010337036883 |
|  5-dobbel horisontal | 1095 09         | 1/5 | 11 | 4010337036920 |
|  5-dobbel loddrett   | 1115 09         | 1   | 11 | 4010337036913 |

## Egenskaper

- Bruddsikker.
  - Sprøytetåketett.
  - Dekkramme med transparent vindu for merking av innsatsene.
  - Spesielt egnet for objekter som krever merking og dokumentasjon av elektroinstallasjon, f.eks. innen forvaltning, næringsvirksomhet, på flyplasser, i bedrifter og på sykehus.
- 

## Merknader

- Må ikke brukes sammen med: tetningssett IP44, påveggboks av flat konstruksjon, påveggboks.
-