










## Dekkramme Gira E2 med tekstfelt renhvit glans



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	1091 29	10	01	4010337084068
 Dobbel horisontal	1092 29	10	01	4010337084129
 Dobbel lodrett	1102 29	10	01	4010337084150
 3-dobbel horisontal	1093 29	1/5	01	4010337084198
 3-dobbel vertikal	1103 29	1/5	01	4010337084235
 4-dobbel horisontal	1094 29	1	01	4010337084273
 4-dobbel loddrett	1114 29	1	01	4010337084310
 5-dobbel horisontal	1095 29	1/5	01	4010337084396
 5-dobbel loddrett	1115 29	1/5	01	4010337084358

## Egenskaper

- Bruddsikker.
  - Sprøytetåketett.
  - Dekkramme med transparent vindu for merking av innsatsene.
  - Spesielt egnet for objekter som krever merking og dokumentasjon av elektroinstallasjon, f.eks. innen forvaltning, næringsvirksomhet, på flyplasser, i bedrifter og på sykehus.
- 

## Merknader

- Må ikke brukes sammen med: tetningssett IP44, påveggboks av flat konstruksjon, påveggboks.
-