









## Dekkramme Gira Standard 55 med tekstfelt kremhvit glans



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	1091 01	10	01	4010337091011
 Dobbel horisontal	1092 01	10	01	4010337092018
 Dobbel lodrett	1102 01	10	01	4010337102014
 3-dobbel horisontal	1093 01	1/5	01	4010337093015
 3-dobbel vertikal	1103 01	1/5	01	4010337103011
 4-dobbel horisontal	1094 01	1/5	01	4010337094012
 4-dobbel loddrett	1114 01	1	01	4010337008903
 5-dobbel horisontal	1095 01	1	01	4010337095019
 5-dobbel loddrett	1115 01	1	01	4010337115014

## Egenskaper

- Bruddsikker.
  - Sprøytetåketett.
  - Dekkramme med transparent vindu for merking av innsatsene.
  - Spesielt egnet for objekter som krever merking og dokumentasjon av elektroinstallasjon, f.eks. innen forvaltning, næringsvirksomhet, på flyplasser, i bedrifter og på sykehus.
- 

## Merknader

- Må ikke brukes sammen med: tetningssett IP44, påveggboks av flat konstruksjon, påveggboks.
-