










## Dekkramme Gira E2 med tekstfelt renhvit silkematt



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	1091 22	10	01	4010337084037
 Dobbel horisontal	1092 22	10	01	4010337084082
 Dobbel lodrett	1102 22	10	01	4010337089131
 3-dobbel horisontal	1093 22	1/5	01	4010337084167
 3-dobbel vertikal	1103 22	1/5	01	4010337084204
 4-dobbel horisontal	1094 22	1/5	01	4010337084242
 4-dobbel loddrett	1114 22	1	01	4010337084280
 5-dobbel horisontal	1095 22	1/5	01	4010337084365
 5-dobbel loddrett	1115 22	1/5	01	4010337084327

## Egenskaper

- Bruddsikker.
  - Sprøytetåketett.
  - Dekkramme med transparent vindu for merking av innsatsene.
  - Spesielt egnet for objekter som krever merking og dokumentasjon av elektroinstallasjon, f.eks. innen forvaltning, næringsvirksomhet, på flyplasser, i bedrifter og på sykehus.
- 

## Merknader

- Må ikke brukes sammen med: tetningssett IP44, påveggboks av flat konstruksjon, påveggboks.
-