








Dekkramme Gira E2 med tekstfelt grå matt



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	1091 37	10	11	4010337082590
 Dobbel horisontal	1092 37	10	11	4010337082651
 Dobbel lodrett	1102 37	10	11	4010337082699
 3-dobbel horisontal	1093 37	1	11	4010337082668
 3-dobbel vertikal	1103 37	1	11	4010337082729
 4-dobbel horisontal	1094 37	1	11	4010337082675
 4-dobbel loddrett	1114 37	1	11	4010337082873
 5-dobbel horisontal	1095 37	1	11	4010337082682
 5-dobbel loddrett	1115 37	1	11	4010337082880

Egenskaper

- Bruddsikker.
 - Sprøytetåketett.
 - Dekkramme med transparent vindu for merking av innsatsene.
 - Spesielt egnet for objekter som krever merking og dokumentasjon av elektroinstallasjon, f.eks. innen forvaltning, næringsvirksomhet, på flyplasser, i bedrifter og på sykehus.
-

Merknader

- Må ikke brukes sammen med: tetningssett IP44, påveggboks av flat konstruksjon, påveggboks.
-