










## Dekkramme Gira E2 med tekstfelt svart matt



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	1091 09	10	11	4010337036746
 Dobbel horisontal	1092 09	10	11	4010337036814
 Dobbel lodrett	1102 09	10	11	4010337036807
 3-dobbel horisontal	1093 09	1/5	11	4010337036852
 3-dobbel vertikal	1103 09	1/5	11	4010337036845
 4-dobbel horisontal	1094 09	1/5	11	4010337036890
 4-dobbel loddrett	1114 09	1	11	4010337036883
 5-dobbel horisontal	1095 09	1/5	11	4010337036920
 5-dobbel loddrett	1115 09	1	11	4010337036913

## Egenskaper

- Bruddsikker.
  - Sprøytetåketett.
  - Dekkramme med transparent vindu for merking av innsatsene.
  - Spesielt egnet for objekter som krever merking og dokumentasjon av elektroinstallasjon, f.eks. innen forvaltning, næringsvirksomhet, på flyplasser, i bedrifter og på sykehus.
- 

## Merknader

- Må ikke brukes sammen med: tetningssett IP44, påveggboks av flat konstruksjon, påveggboks.
-