










Dekkramme Gira E2 med tekstfelt antrasitt



| Spesifikasjon | Bestillings nr. | PE | PS | EAN |
|---|-----------------|-----|----|---------------|
|  Enkel | 1091 23 | 10 | 11 | 4010337084044 |
|  Dobbel horisontal | 1092 23 | 10 | 11 | 4010337084099 |
|  Dobbel lodrett | 1102 23 | 10 | 11 | 4010337089148 |
|  3-dobbel horisontal | 1093 23 | 1/5 | 11 | 4010337084174 |
|  3-dobbel vertikal | 1103 23 | 1/5 | 11 | 4010337084211 |
|  4-dobbel horisontal | 1094 23 | 1 | 11 | 4010337084259 |
|  4-dobbel loddrett | 1114 23 | 1/5 | 11 | 4010337084297 |
|  5-dobbel horisontal | 1095 23 | 1 | 11 | 4010337084372 |
|  5-dobbel loddrett | 1115 23 | 1 | 11 | 4010337084334 |

Egenskaper

- Bruddsikker.
 - Sprøytetåketett.
 - Dekkramme med transparent vindu for merking av innsatsene.
 - Spesielt egnet for objekter som krever merking og dokumentasjon av elektroinstallasjon, f.eks. innen forvaltning, næringsvirksomhet, på flyplasser, i bedrifter og på sykehus.
-

Merknader

- Må ikke brukes sammen med: tetningssett IP44, påveggboks av flat konstruksjon, påveggboks.
-