










Dekkramme Gira E2 med tekstfelt antrasitt



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	1091 23	10	11	4010337084044
 Dobbel horisontal	1092 23	10	11	4010337084099
 Dobbel lodrett	1102 23	10	11	4010337089148
 3-dobbel horisontal	1093 23	1/5	11	4010337084174
 3-dobbel vertikal	1103 23	1/5	11	4010337084211
 4-dobbel horisontal	1094 23	1	11	4010337084259
 4-dobbel loddrett	1114 23	1/5	11	4010337084297
 5-dobbel horisontal	1095 23	1	11	4010337084372
 5-dobbel loddrett	1115 23	1	11	4010337084334

Egenskaper

- Bruddsikker.
 - Sprøytetåketett.
 - Dekkramme med transparent vindu for merking av innsatsene.
 - Spesielt egnet for objekter som krever merking og dokumentasjon av elektroinstallasjon, f.eks. innen forvaltning, næringsvirksomhet, på flyplasser, i bedrifter og på sykehus.
-

Merknader

- Må ikke brukes sammen med: tetningssett IP44, påveggboks av flat konstruksjon, påveggboks.
-