










**Dekkramme Gira E2 med tekstfelt
aluminiumsfarget**



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	1091 25	10	11	4010337084051
 Dobbel horisontal	1092 25	10	11	4010337084112
 Dobbel lodrett	1102 25	10	11	4010337084143
 3-dobbel horisontal	1093 25	1/5	11	4010337084181
 3-dobbel vertikal	1103 25	1/5	11	4010337084228
 4-dobbel horisontal	1094 25	1/5	11	4010337084266
 4-dobbel loddrett	1114 25	1/5	11	4010337084303
 5-dobbel horisontal	1095 25	1	11	4010337084389
 5-dobbel loddrett	1115 25	1/5	11	4010337084341

Egenskaper

- Bruddsikker.
 - Sprøytetåketett.
 - Dekkramme med transparent vindu for merking av innsatsene.
 - Spesielt egnet for objekter som krever merking og dokumentasjon av elektroinstallasjon, f.eks. innen forvaltning, næringsvirksomhet, på flyplasser, i bedrifter og på sykehus.
-

Merknader

- Må ikke brukes sammen med: tetningssett IP44, påveggboks av flat konstruksjon, påveggboks.
-