










**Dekkramme Gira E2 med tekstfelt
renhvit silkematt**



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	1091 22	10	01	4010337084037
 Dobbel horisontal	1092 22	10	01	4010337084082
 Dobbel lodrett	1102 22	10	01	4010337089131
 3-dobbel horisontal	1093 22	1/5	01	4010337084167
 3-dobbel vertikal	1103 22	1/5	01	4010337084204
 4-dobbel horisontal	1094 22	1/5	01	4010337084242
 4-dobbel loddrett	1114 22	1	01	4010337084280
 5-dobbel horisontal	1095 22	1/5	01	4010337084365
 5-dobbel loddrett	1115 22	1/5	01	4010337084327

Egenskaper

- Bruddsikker.
 - Sprøytetåketett.
 - Dekkramme med transparent vindu for merking av innsatsene.
 - Spesielt egnet for objekter som krever merking og dokumentasjon av elektroinstallasjon, f.eks. innen forvaltning, næringsvirksomhet, på flyplasser, i bedrifter og på sykehus.
-

Merknader

- Må ikke brukes sammen med: tetningssett IP44, påveggboks av flat konstruksjon, påveggboks.
-