






Dekkramme Gira E2 med tekstfelt aluminiumsfarget



Spesifikasjon	Bestillings nr.	PE	PS	EAN
 Enkel	1091 25	10	11	4010337084051
 Dobbel horisontal	1092 25	10	11	4010337084112
 Dobbel lodrett	1102 25	10	11	4010337084143
 3-dobbel horisontal	1093 25	1/5	11	4010337084181
 3-dobbel vertikal	1103 25	1/5	11	4010337084228
 4-dobbel horisontal	1094 25	1/5	11	4010337084266
 4-dobbel loddrett	1114 25	1/5	11	4010337084303
 5-dobbel horisontal	1095 25	1	11	4010337084389
 5-dobbel loddrett	1115 25	1/5	11	4010337084341

Egenskaper

- Bruddsikker.
 - Sprøytetåketett.
 - Dekkramme med transparent vindu for merking av innsatsene.
 - Spesielt egnet for objekter som krever merking og dokumentasjon av elektroinstallasjon, f.eks. innen forvaltning, næringsvirksomhet, på flyplasser, i bedrifter og på sykehus.
-

Merknader

- Må ikke brukes sammen med: tetningssett IP44, påveggboks av flat konstruksjon, påveggboks.
-