

**Dekkramme Gira Standard 55 med tekstfelt
kremhvit glans**



| Spesifikasjon | Bestillings nr. | PE | PS | EAN |
|---|-----------------|-----|----|---------------|
|  Enkel | 1091 01 | 10 | 01 | 4010337091011 |
|  Dobbel vannrett | 1092 01 | 10 | 01 | 4010337092018 |
|  Dobbel lodrett | 1102 01 | 10 | 01 | 4010337102014 |
|  3-dobbel vannrett | 1093 01 | 1/5 | 01 | 4010337093015 |
|  3-dobbel vertikal | 1103 01 | 1/5 | 01 | 4010337103011 |
|  4-dobbel vannrett | 1094 01 | 1/5 | 01 | 4010337094012 |
|  4-dobbel loddrett | 1114 01 | 1 | 01 | 4010337008903 |
|  5-dobbel vannrett | 1095 01 | 1 | 01 | 4010337095019 |
|  5-dobbel loddrett | 1115 01 | 1 | 01 | 4010337115014 |

Egenskaper

- Bruddsikker.
 - Sprøytetåketett.
 - Dekkramme med transparent vindu for merking av innsatsene.
 - Spesielt egnet for objekter som krever merking og dokumentasjon av elektroinstallasjon, f.eks. innen forvaltning, næringsvirksomhet, på flyplasser, i bedrifter og på sykehus.
-

Merknader

- Må ikke brukes sammen med: tetningssett IP44, påveggbus av flat konstruksjon, påveggbus.
-